












品番	1-5428-21	1-5432-21	1-5433-21	1-5434-21	1-5435-21	1-5430-21	1-5431-21	1-5438-21	1-5439-21	2-6410-01	1-5440-01
型番	MASTER-A1T	MASTER-A2T	MASTER-A3T	MASTER-A4T	MASTER-A53T	MASTER-A10T	MASTER-A20T	MASTER-AH50	MASTER-AH80	N-8 α	I-500
測定範囲 (%)	 Brix0.0~33.0	 Brix28.0~62.0	 Brix58.0~90.0	 Brix45.0~82.0	 Brix0.0~53.0	 Brix0.0~10.0	 Brix0.0~20.0	 Brix0.0~50.0	 Brix30.0~80.0	 Brix0.0~8.0	 Brix0.0~90.0
測定精度 (%)	Brix $\pm$ 0.2 (10~30℃)	Brix $\pm$ 0.2 (10~40℃)			Brix $\pm$ 0.5 (10~30℃)	Brix $\pm$ 0.2 (10~30℃)		Brix $\pm$ 0.5 (10~30℃)	Brix $\pm$ 0.5 (10~40℃)	—	
最小目盛 (%)	Brix0.2				Brix0.5	Brix0.1		Brix0.5		Brix0.1	Brix0.2
繰り返し性 (%)	$\pm$ 0.1				$\pm$ 0.25	$\pm$ 0.1		$\pm$ 0.25		—	
自動温度補正	○									—	
サイズ (mm)	33×33×204		33×33×168			33×33×204		33×33×168		40×40×210	40×40×200
重量 (g)	160		120			160		120		260	600
価格 (税抜)	¥16,000	¥16,000	¥16,000	¥16,000	¥16,000	¥16,000	¥16,000	¥25,000	¥25,000	¥28,000	¥45,000
照会No.	034065	034065	034065	034065	034065	034065	034065	034065	034065	034085	034075

※AH50・AH80はプリズム面に滴下するサンプル温度は100℃以下にしてください。